

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock #16-863 3-4 DAYS



1



€615,00

ADD TO CART

Qty 1+

€615,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1600

Groove Density Uniformity (grooves/mm):
0.001

Design Wavelength DWL (nm):
1030 ±10

Minimum Efficiency (%): ≥94 @ 1030nm
Dimensions (mm): 31.80 x 12.30
Angle of Incidence (°): 55.5 ±1
Clear Aperture CA (mm): 30.80 x 11.30
Coating: Dielectric
Construction: Multi-Layer Dielectric Binary Etch Grating
Length (mm): 31.80
Model Number: 1304192
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 60-40
Thickness (mm): 0.95 ±0.050
Type: Transmission Diffraction Grating
Width (mm): 12.30
Alignment of Grooves to Edge (°): 0.1 (typical)
Polarization: S
Note: S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View