

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock #16-875 3-4 DAYS



1



€615,00

ADD TO CART

Qty 1+

€615,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
966.18

Groove Density Uniformity (grooves/mm):
0.001

Wavelength Range (nm):
1525 - 1565

Minimum Efficiency (%) : ≥92 @ 1525 - 1565nm
Dimensions (mm) : 27.00 x 10.00
Angle of Incidence (°) : 48.3 ±1
Clear Aperture CA (mm) : 26.00 x 9.00
Coating : Dielectric
Construction : Multi-Layer Dielectric Binary Etch Grating
Length (mm) : 27.00
Model Number : 1304279
Substrate :  Fused Silica (Corning 7980)
Surface Quality : 60-40
Thickness (mm) : 0.68 ±0.050
Type : Transmission Diffraction Grating
Width (mm) : 10.00
Alignment of Grooves to Edge (°) : 0.1 (typical)
Polarization : S and P
Note : S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View