

Coherent® LightSmyth™ 800nm, 1398.6 Grooves/mm, 130 x 14.9mm Transmission Diffraction Grating

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock #16-861 3-4 DAYS

- 1 + **€3.480,00**

ADD TO CART

Qty 1+
€3.480,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1398.6

Groove Density Uniformity (grooves/mm):
0.001

Design Wavelength DWL (nm):
800 ±20

Minimum Efficiency (%) : ≥94 @ 800nm
Dimensions (mm) : 130.00 x 14.90
Angle of Incidence (°) : 34 ±1
Clear Aperture CA (mm) : 125.00 x 13.90
Coating : Dielectric
Construction : Multi-Layer Dielectric Binary Etch Grating
Length (mm) : 130.00
Model Number : 1304166
Substrate :  Fused Silica (Corning 7980)
Surface Quality : 60-40
Thickness (mm) : 0.95 ±0.050
Type : Transmission Diffraction Grating
Width (mm) : 14.90
Alignment of Grooves to Edge (°) : 0.1 (typical)
Polarization : S and P
Note : S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View