

LightPath 354220 | 543nm Alignment, 0.25 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #16-705 3-4 DAYS



1



€270,00

ADD TO CART

Qty 1-5

€270,00

Qty 6+

€198,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.25

Substrate: D-ZK3
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.50
f#: 2.00
Bevel: Protective bevel as needed
Connector: FC/APC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 22.43
Lightpath Lens Code: 354220
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite
Alignment Wavelength (nm): 543

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant