

TECHSPEC® Infinite Conjugate, Gold Coated, 20X/0.33NA RefIX Objective



Stock **#39-143** 3-4 DAYS

- 1 + **€2.341,00**

ADD TO CART

Qty 1+
€2.341,00
Qty 2+
€2.106,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Entrance Pupil Position (mm):
7 (Diameter)

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Focal Length FL (mm):

10.06
Coating: Protected Gold (700-11000nm)
Magnification: 20X
Numerical Aperture NA: 0.33
Mounting Threads: RMS
Type: Microscope Objective
Obscuration (%): 30.19
Transmitted Wavefront, RMS: λ/10
Diameter of Small Mirror (mm): 8.4
Working Distance (mm): 18.88
Aperture Diameter (mm): 7.9
Note: Requires a 200mm secondary tube lens
Coating Specification: R _{avg} >96% @ 700 - 11000nm (typical)
Wavelength Range (nm): 700 - 11000
Style: Infinity Corrected
Manufacturer: Edmund Optics®

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View