

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® Infinite Conjugate, UV Coated, 10X/0.22NA Retix Objective



Stock #89-724 3-4 DAYS

- 1 + €2.009,00

ADD TO CART

Qty 1+

€2.009,00

Qty 2+

€1.770,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Entrance Pupil Position (mm):
8.4921 (Diameter)

Horizontal Field of View, 1/2" Sensor:
0.64mm

Horizontal Field of View, 2/3" Sensor:
0.88mm

Focal Length FL (mm):

19.30
Coating: Enhanced Aluminum (200-11000nm)
Magnification: 10X
Numerical Aperture NA: 0.22
Mounting Threads: RMS
Type: Microscope Objective
Obscuration (%) : 27.00
Transmitted Wavefront, RMS: λ/10
Diameter of Small Mirror (mm): 8.9
Working Distance (mm): 30.56
Aperture Diameter (mm): 8.6
Note: Requires a 200mm secondary tube lens
Coating Specification: R _{avg} >85% @ 200 - 700nm (typical) R _{avg} >76% @ 700 - 1750nm (typical) R _{avg} >96% @ 1750 - 11000nm (typical)
Wavelength Range (nm): 200 - 11000
Style: Infinity Corrected
Manufacturer: Edmund Optics®

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View