

LightPath 354240 | 543nm Alignment, 0.50 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #16-709 3-4 DAYS

1

€270,00

ADD TO CART

Qty 1-5

€270,00

Qty 6+

€198,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
8.00 @ 780nm

Numerical Aperture NA:
0.50

Substrate: D-ZK3
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 8.00
f/#: 1.00
Bevel: Protective bevel as needed
Connector: FC/APC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 12.00
Housing Length (mm): 17.91
Lightpath Lens Code: 354240
Mount: M12 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite
Alignment Wavelength (nm): 543

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant