

Olympus UPLXAPO 60X Oil Immersion Objective

See More by [Olympus](#)



Olympus X-Line Extended Apochromat Objectives



Stock **#14-909** [CONTACT US](#)



1



€7.617,00

ADD TO CART

Qty 1+

€7.617,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
0.44

Focal Length FL (mm):
3.00

Model Number: UPLXAPO60XO
Length excluding Threads (mm): 44.88
Magnification: 60X
Maximum Diameter (mm): 31.5
Numerical Aperture NA: 1.42
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.24
Depth of Field (µm): 0.21
Working Distance (mm): 0.15
Weight (g): 166
Note: Spring-loaded. Recommended Immersion Oil #86-834
Wavelength Range (nm): 300 - 1000
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45.06
Immersion Liquid: Oil
Regulatory Compliance
Certificate of Conformance: View