

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

PL-D753CU-AF-ED Pixelink USB 3.0 Autofocus Color Camera



Stock #14-181 [CONTACT US](#)

[Similar Cameras](#)

1 **€1.500,00**

ADD TO CART

Qty 1+

€1.500,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Camera

Manufacturer:
Pixelink

Mounting Threads: ¼-20 with Tripod Mount Adapter #34-949
Image Buffer: Not Specified
Camera Family: PL-D
Model Number: PL-D753CU-AF-ED
Imaging Sensor: Sony IMX421
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 3.00
Pixels (H x V): 1,936 x 1,464
Pixel Size, H x V (µm): 4.5 x 4.5
Sensing Area, H x V (mm): 8.71 x 6.59
Frame Rate (fps): 141.10
Pixel Depth: 8/12 bit
Exposure Time: 10µs - 120s
Connector: USB 3.0, Micro-B with Screw Locks
Power Supply: Power over USB
Power Consumption (W): Not Specified
GPIOs: 1 opto-isolated trigger input, 1 opto-isolated output, 2 non-isolated outputs, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 55 x 38.5 x 27 (excludes connectors and lens mount)
Weight (g): 35.8
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 72
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -45 to +85
GPIO Connector Type: 8-pin Hirose (HR25)
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View