

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Quartz Rochon Polarizer



Stock #68-824 3-4 DAYS



1



€785,00

ADD TO CART

Qty 1+

€785,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
10.0

Diameter (mm):
25.40

Extinction Ratio:
20,000:1

Substrate: ☐ Crystal Quartz

Length (mm):
28.00

Surface Quality: 20-10
Type: Linear Polarizer
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Crystalline Rochon Polarizer
Transmitted Wavefront, P-V: λ/4 @ 632.8nm
Length Tolerance (mm): ±0.1
Beam Deviation (arcmin): <3
Housing: Black Anodized Aluminum
Wavelength Range (nm): 200 - 2300
Damage Threshold, By Design: 10 J/cm² @ 1064nm, 20ns
Separation Angle (°): 1.0 - 1.5 (1 @ 1064nm)

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View