

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union



SUBMIT

Replacement Unmounted window for 800nm, 0.80 NA, apianoXX Apian Objective

See More by [AdiOptica](#)



Replacement Window

Stock #19-494 3-4 DAYS



1



€97,00

ADD TO CART

Qty 1+

€97,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8

Design Wavelength DWL (nm):
800

Diameter (mm):
12.00

Model Number:
Protective Wndow_D12_800

Type: Protective Window
Note: Protective window for #19-492 , #19-496
Wavelength Range (nm): 770 - 900
Damage Threshold, By Design: ☐ 25 mJ @ 5ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant