

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union



SUBMIT

SCHOTT NG11, 0.1 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #16-717 3-4 DAYS



1



€26,00

ADD TO CART

Qty 1-10

€26,00

Qty 11+

€23,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Optical Density OD (Average):
0.1 ±0.006 @ 546nm

Glass/Filter Number:
[SCHOTT NG11](#)

Coating: Uncoated
Index of Refraction n_d: 1.50
Surface Quality: 80-50
Transformation Temperature (°C): 481
Thickness (mm): 0.60
Thickness Tolerance (mm): (nominal)
Transmission (%): 79.43 ±1.03% @ 546nm
Type: Neutral Density Filter
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
Reach 240: Compliant
