

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

M2590, 1" NIR, Teledyne Dalsa Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne Dalsa Genie™ Nano GigE Power over Ethernet (PoE) Cameras



Stock #14-677 3-4 DAYS



1



€1.085,00

ADD TO CART

Qty 1+

€1.085,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
GigE (PoE)

Type:
NIR Camera

Manufacturer:
Teledyne Dalsa

Mounting Threads: ¼-20 with Tripod Mount Adapter #34-966
Image Buffer: 90MB
Camera Family: Genie Nano-1GigE
Model Number: Nano-M2590 NIR
Imaging Sensor: ON Semi PYTHON 5000
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1"
Resolution (MegaPixels): 5.30
Pixels (H x V): 2,592 x 2,048
Pixel Size, H x V (µm): 4.8 x 4.8
Sensing Area, H x V (mm): 12.44 x 9.83
Frame Rate (fps): 22.70
Pixel Depth: 8/10 bit
Exposure Time: Programmable or via external trigger
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power over Ethernet (PoE) or via GPIO
Power Consumption (W): 3.6 - 4.6 (12VDC External Power Supply) 4.0 - 4.9 (PoE)
GPIOs: 2 digital input, 2 digital output
Synchronization: Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)
Dimensions (mm): 40.6 x 29.0 x 44.0 (includes connectors and lens mount)
Weight (g): 46
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 62.1
Operating Temperature (°C): -20 to +60
Storage Temperature (°C): -40 to +80
GPIO Connector Type: 10-pin Samtec
Machine Vision Standard: GigE Vision v1.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View