


In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union



SUBMIT



Acktar Light Absorbent Foil



Stock #12-695 ☐ In Stock



1



€112,00

ADD TO CART

Qty 1-5

€112,00

Qty 6+

€99,30

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Metal Velvet™

Model Number: MV-20X20-1
Operating Temperature (°C): -40 to +121
Dimensions (mm): 200 x 200
Type: Standard Adhesive
Coating Thickness (µm): 5 - 7
Foil Thickness (µm): 115
Abrasion Resistance: Light, do not touch
Adhesive Thickness (µm): 60
Humidity Resistance: ML-C-48497A
Wavelength Range (µm): 0.3 - 14
Dimensions (cm): 20 x 20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant