

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union




SUBMIT

200 X 600mm Sheet of Metal Velvet Foil, Low Outgassing Adhesive

See More by [Acktar](#)



Acktar Light Absorbent Foil



Stock #12-516 3-4 DAYS



1



€350,50

ADD TO CART

Qty 1-5

€350,50

Qty 6+

€315,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Metal Velvet™

Model Number: MV-20X060-3
Operating Temperature (°C): -40 to +150
Dimensions (mm): 200 x 600
Type: Low Outgassing Adhesive
Coating Thickness (µm): 5 - 8
Foil Thickness (µm): 115
Abrasion Resistance: Light, do not touch
Adhesive Thickness (µm): 60
Humidity Resistance: ML-C-48497A
Wavelength Range (µm): 0.3 - 14
Dimensions (cm): 20 x 60
Note: Typical Adhesive Outgassing Performance: 0.85% TML, 0% VCM per ASTM E595-77/84/90

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant