

# SCHOTT NG9, 25mm Dia., 2mm Thick, Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock **#14-101** ☐ In Stock

-

1

+

**€42,00**

ADD TO CART

|                                                                                 |
|---------------------------------------------------------------------------------|
| Qty 1-10                                                                        |
| €42,00                                                                          |
| Qty 11+                                                                         |
| €37,00                                                                          |
| Volume Pricing                                                                  |
| <a href="#">Request Quote</a>                                                   |
| <div><div>!</div><div>Prices shown are exclusive of VAT/local taxes</div></div> |

## Get Product Downloads

**Diameter (mm):**  
25.00

**Optical Density OD (Average):**  
2.8

|                                                                |
|----------------------------------------------------------------|
| <div>Glass/Filter Number:<br/><a href="#">SCHOTT NG9</a></div> |
| <div>Coating:<br/>Uncoated</div>                               |
| <div>Index of Refraction <math>n_d</math>:<br/>1.51</div>      |
| <div>Surface Quality:<br/>60-40</div>                          |
| <div>Transformation Temperature (°C):<br/>470</div>            |
| <div>Thickness (mm):<br/>2.00 ±0.2</div>                       |
| <div>Transmission (%):<br/>0.15</div>                          |
| <div>Transmission Tolerance (%):<br/>(nominal)</div>           |
| <div>Type:<br/>Neutral Density Filter</div>                    |
| <div>Parallelism (arcmin):<br/>≤3</div>                        |
| <div>Dimensional Tolerance (mm):<br/>±0.2</div>                |
| <div>Optical Density Tolerance (%):<br/>(nominal)</div>        |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Reach 223:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |