


# Microlens Array 10 x 10mm, 500µm Pitch, 1.2° Divergence, VIS-NIR Coated



Microlens Arrays



Stock #15-813 3-4 DAYS

⊖ 1 ⊕

€805,00

ADD TO CART

|                               |         |
|-------------------------------|---------|
| Qty 1-10                      | €805,00 |
| Qty 11+                       | €724,00 |
| Volume Pricing                |         |
| <a href="#">Request Quote</a> |         |

ⓘ Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

Effective Focal Length EFL (mm):  
13.80

Substrate: [Fused Silica](#) (Corning 7980)

|                                                                                                                                                     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Coating:</b><br>VIS-NIR (400-1000nm)                                                                                                             |
| <b>Type:</b><br>Lens Array                                                                                                                          |
| <b>Wavelength Range (nm):</b><br>400 - 1000                                                                                                         |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm |
| <b>Dimensional Tolerance (mm):</b><br>±0.05                                                                                                         |
| <b>Dimensions (mm):</b><br>10.0 x 10.0                                                                                                              |
| <b>Divergence Angle (°):</b><br>±1.2                                                                                                                |
| <b>Lens Profile:</b><br>Spherical                                                                                                                   |
| <b>Pitch (µm):</b><br>500.00                                                                                                                        |
| <b>Pitch Tolerance (µm):</b><br>±0.25                                                                                                               |
| <b>Radius R (mm):</b><br>6.30                                                                                                                       |
| <b>Thickness (mm):</b><br>1.20                                                                                                                      |
| <b>Thickness Tolerance (mm):</b><br>±0.05                                                                                                           |
| <b>Type of Optics:</b><br>Plano-Convex                                                                                                              |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |