

Mounted Window for 800nm, 0.80 NA, aplanoXX Aplan Objective

See More by [AdlOptica](#)



Mounted Window

Stock **#19-496** 3-4 DAYS



1



€301,00

ADD TO CART

Qty 1+

€301,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8

Design Wavelength DWL (nm):
800

Diameter (mm):
29.50

Model Number:
Window in Holder L9333.06 (+D12 800)

Length (mm): 4.40
Type: Mounted Window
Note: Protective window for #19-492
Wavelength Range (nm): 770 - 900
Damage Threshold, By Design: ☐ 25 mJ @ 5ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant