

In order to provide more accurate inventory information, please select your shipping country.


Select Your Country/Region: European Union



SUBMIT

SCHOTT NG9, 4.0 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #16-657 3-4 DAYS



1



€26,00

ADD TO CART

Qty 1-10

€26,00

Qty 11+

€23,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Optical Density OD (Average):
4.0 ±0.07 @ 546nm

Glass/Filter Number:
[SCHOTT NG9](#)

Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 470
Thickness (mm): 2.90
Thickness Tolerance (mm): (nominal)
Transmission (%): 0.010 ±0.0017% @ 546nm
Type: Neutral Density Filter
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View