

VZM™ 1000i Zoom Imaging Lens



VZM™ 1000i

Stock **#55-834** 3-4 DAYS



1



€1.155,00

ADD TO CART

Qty 1+

€1.155,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
247.00

Horizontal Field of View, 1/2" Sensor:
2.56 - 0.64mm

Horizontal Field of View, 2/3" Sensor:
3.52 - 0.88mm

Filter Thread:
M22.5 x0.50

Maximum Diameter (mm):

50.00
Weight (g): 326.00
Working Distance Tolerance (mm): ±1
Resolution, Object Space: 102.5 - 228
Resolution, Image Space: 41 - 22.8
Zoom Ratio: 4:1
Type: Zoom Lens
Primary Magnification PMAG: 2.5X - 10X
Maximum Sensor Format: 2/3"
Working Distance (mm): 35.00
Mount: C-Mount
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View