



Replacement Window for 515/1030nm foXXus and aplanoXX Objectives

See More by [AdlOptica](#)



Replacement Window



Stock **#19-493** 3-4 DAYS

⊖ 1 ⊕ **€97,00**

ADD TO CART

Qty 1+

€97,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8

Design Wavelength DWL (nm):
515, 1030

Diameter (mm):
12.00

Model Number: Protective Window_D12_515/1030
Type: Protective Window
Note: Protective window for #19-491 , #19-495 , #19-498 , #19-499 , #19-501
Wavelength Range (nm): 510 - 545, 1020 - 1100
Damage Threshold, By Design: ☐ 25 mJ @ 5ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant