

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

LightPath 390010 | 4.5mm Dia., 0.83 NA, BBAR (8000-12000nm), Molded IR Aspneric Lens

See More by [Lightpath®](#)



Stock #88-073 3-4 DAYS



1



€360,00

ADD TO CART

Qty 1-10

€360,00

Qty 11+

€317,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

4.50 ±0.015

Effective Focal Length EFL (mm):

1.47 @9200nm

Numerical Aperture NA:

0.83

Substrate:  Black Diamond™ BD-2 (Ge ₂₈ Sb ₁₂ Se ₆₀)
Aspheric Design Wavelength (nm): 9200
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} <1.0% @ 8 - 12μm
Surface Quality: 80-50
Clear Aperture CA (mm): 3.00
Edge Thickness ET (mm): 1.63
Center Thickness CT (mm): 2.17
f/#: 0.6
Bevel: Protective bevel as needed
Density (g/cm³): 4.68
Index of Refraction n_d @ 10μm: 2.6023
Index of Refraction n_d @ 14μm: 2.5843
Index of Refraction n_d @ 4μm: 2.6210
Index of Refraction n_d @ 5μm: 2.6173
Lightpath Lens Code: 390010
Thermo-optic coefficient dn/dT: 70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm)
Transformation Temperature (°C): 285.00
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Working Distance (mm): 0.63
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant