

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

# NOV-VIS-NIR Nd:YAG Laser Line Vertical Mitutoyo video Microscope Unit

See More by [Mitutoyo](#)



#89-622 + Objective

Stock #89-622 3-4 DAYS



1



€7.140,00

ADD TO CART

Qty 1+

€7.140,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):  
355, 532, 1064

Model Number:  
VMU-L

Magnification:  
1X

Maximum Sensor Format:  
2/3"

|                                                                                                                                        |
|----------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mount:</b><br>C-Mount                                                                                                               |
| <b>Range:</b><br>NUV-VIS-NIR                                                                                                           |
| <b>Mounting Threads:</b><br>Objective Mounts: M26 x 36 TPI                                                                             |
| <b>Type:</b><br>Vertical Mount, Brightfield, erect image                                                                               |
| <b>Weight (g):</b><br>980.00                                                                                                           |
| <b>Note:</b><br>Note: Magnification: 1X Tube Lens<br>Optional C-Mount adapter <a href="#">#37-044</a> available for dual-camera system |
| <b>Manufacturer:</b><br>Mitutoyo                                                                                                       |
| <b>Compatible Objectives:</b><br><a href="#">M Plan Apo/HR/SL</a> and <a href="#">M Plan NIR/NUV</a>                                   |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Reach 224:</b><br><a href="#">Contains SVHC(s)</a>      |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |