

# SCHOTT NG4, 0.6 OD, 25mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #16-663 3-4 DAYS

⊖ 1 ⊕ **€42,00**

ADD TO CART

Qty 1-10

€42,00

Qty 11+

€37,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
25.00

Optical Density OD (Average):  
0.6 ±0.03 @ 546nm

Glass/Filter Number:  
[SCHOTT NG4](#)

|                                                      |
|------------------------------------------------------|
| <b>Coating:</b><br>Uncoated                          |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.51 |
| <b>Surface Quality:</b><br>80-50                     |
| <b>Transformation Temperature (°C):</b><br>483       |
| <b>Thickness (mm):</b><br>1.10                       |
| <b>Thickness Tolerance (mm):</b><br>(nominal)        |
| <b>Transmission (%):</b><br>25.12 ±1.51% @ 546nm     |
| <b>Type:</b><br>Neutral Density Filter               |
| <b>Dimensional Tolerance (mm):</b><br>±0.38          |
| <b>Wavelength Range (nm):</b><br>400 - 700           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |

---