## NOTES:

1. SUBSTRATE MATERIAL: SCHOTT: N-BK7 517/642

**EQUIVALENT SUBSTITUTIONS ALLOWED** 


- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: <3 arc min.
- 3. COATING(APPLY ACROSS CLEAR APERTURE)
  \$1, \$2, \$3, & \$4: 1/4 WAVE MGF2 @ 550nm
  \$5: MULTILAYER DIELECTRIC TO ACHIEVE
  R(ABS) = 50% ±5% @ 550nm
  T(ABS) = 50% ±5% @ 550nm
  R(AVG) = 50% ±10% FROM 400 TO 700nm
  T(AVG) = 50% ±10% FROM 400 TO 700nm

4. FINE GROUND SURFACE

SELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61

6. PROTECTIVE BEVEL AS NEEDED

AMARK IDENTIFIES BEAMSPLITTER COATED RIGHT ANGLE PRISM



## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			EFL (AT 587.6nm)	NA	<b>Edmund Optics®</b>		
	\$1, \$2, \$3, \$4	\$5	(AT 567.6HH)				
SHAPE	PLANO	PLANO	BFL (AT 587.6nm)	NA	TITLE	20mm 50R/50T Standard Cube Beamsplitter	
SURFACE ACCURACY AT 632.8nm (P-V)	1/4 WAVE	1/4 WAVE					
SURFACE QUALITY	60 - 40	60 - 40					CLIEFT
MIN CLEAR APERTURE	19.0 x 19.0mm	27.2 x 19.0mm	ALL DIMS IN	mm	DWG NO	32504	SHEET 1 OF 1