

SCHOTT NG9, 3.3 OD, 50mm Sq., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-062** ☐ In Stock

-

1

+

€93,00

ADD TO CART

Qty 1-10

€93,00

Qty 11+

€82,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
3.3 ±0.07 @ 546nm

Glass/Filter Number:
[SCHOTT NG9](#)

Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 470
Thickness (mm): 2.40
Thickness Tolerance (mm): (nominal)
Transmission (%): 0.050 ±0.0085% @ 546nm
Type: Neutral Density Filter
Width (mm): 50.00
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Reach 223: Compliant
Certificate of Conformance: View