

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union




SUBMIT

200 X 300mm Sheet of Spectral Black Foil, Low Outgassing Adhesive

See More by [Acktar](#)



Acktar Light Absorbent Foil



Stock #12-517 3-4 DAYS



1



€181,00

ADD TO CART

Qty 1-5

€181,00

Qty 6+

€161,90

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:  
Spectral Black™

|                                                                                                      |
|------------------------------------------------------------------------------------------------------|
| <b>Model Number:</b><br>SB-20X030-3                                                                  |
| <b>Operating Temperature (°C):</b><br>-40 to +150                                                    |
| <b>Dimensions (mm):</b><br>200 x 300                                                                 |
| <b>Type:</b><br>Low Outgassing Adhesive                                                              |
| <b>Coating Thickness (µm):</b><br>3 - 7                                                              |
| <b>Foil Thickness (µm):</b><br>125                                                                   |
| <b>Abrasion Resistance:</b><br>Moderate                                                              |
| <b>Adhesive Thickness (µm):</b><br>60                                                                |
| <b>Humidity Resistance:</b><br>ML-C-48497A                                                           |
| <b>Wavelength Range (µm):</b><br>0.3 - 14                                                            |
| <b>Dimensions (cm):</b><br>20 x 30                                                                   |
| <b>Note:</b><br>Typical Adhesive Outgassing Performance: 0.85%<br>TML, 0% VCM per ASTM E595-77/84/90 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |