

UV-VIS and IR High Power Laser Beam Visualizer



High Power Laser Beam Visualizers

Stock **#11-449** ☐ In Stock



1



€104,40

ADD TO CART

Qty 1-24

€104,40

Qty 25+

€93,96

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Active Area Diameter (mm):
35

Outer Diameter (mm):
42

Dimensions (mm):

Disk: 42 Dia.
Wand: 130 Length

Wavelength:
UV, VIS, IR

Damage Threshold, By Design: ☐
Typical: 1 J/cm² @ 10ns

Emission Color:
Red

Stimulation Range:
190 - 1090nm, 1470 - 1600nm

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)