

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Partial Housing (Front)



Stock #14-882 3-4 DAYS

[Similar Cameras](#)



1



€851,00

ADD TO CART

Qty 1+

€851,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type:
Color Camera

Manufacturer: Allied Vision
Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium
Model Number: 1800 U-507c
Imaging Sensor: Sony IMX264
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 5.10
Pixels (H x V): 2,464 x 2,056
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 8.5 x 7.1
Frame Rate (fps): 34.00
Pixel Depth: 8/10/12 bit
Exposure Time: 176µs - 10s
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 2.0
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 30 x 29 x 29 (includes connectors and lens mount)
Weight (g): 45
Mount: C-Mount
Housing: Partial
Interface Port Orientation: Back Panel
Operating Temperature (°C): -20 to +65 (housing temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant