

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



USB 3.0 FLIR Chameleon Camera



Stock #36-077 3-4 DAYS



1



€889,00

ADD TO CART

Qty 1+

€889,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer:

FLIR

Mounting Threads: ¼-20 with Tripod Mount Adapter #88-210
Image Buffer: 16MB
Camera Family: Chameleon@3
Model Number: CMB-U3-50S5M-CS
Imaging Sensor: Sony IMX264
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 5.00
Pixels (H x V): 2,448 x 2,048
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 8.45 x 7.07
Frame Rate (fps): 35.00
Pixel Depth: 12 bit
Exposure Time: 13µs - 31.995s
Connector: USB 3.1 Gen 1, Micro-B with Screw Locks
Power Supply: Power over USB or via GPIO
Power Consumption (W): Not Specified
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports
Synchronization: Hardware Trigger (GPIO)
Dimensions (mm): 44 x 35 x 22.1 (excludes connectors and lens mount)
Weight (g): 54.9
Mount: CS-Mount
Housing: Full
Interface Port Orientation: Side Panel
Dynamic Range (dB): 70.97
Operating Temperature (°C): 0 to +45
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 9-pin JST
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View