

TECHSPEC® Elliptical Mirror 66.68mm Minor Axis UV Enhanced Aluminum



Stock **#43-580** 3-4 DAYS

- 1 + **€358,00**

ADD TO CART

Qty 1-5
€358,00
Qty 6+
€286,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Minor Axis (mm):
66.68

Major Axis (mm):
94.28

Surface Flatness (P-V):
λ/8

Substrate: 
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.38
Dimensional Tolerance (inches): ±0.015 minor, ±0.015 major
Coating Specification: R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Clear Aperture CA (mm): 60.02 (Minor Axis) 84.86 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 15.88
Thickness Tolerance (inches): ±0.060
Thickness Tolerance (mm): ±1.52
Type: Flat Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference:  0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant