


Microlens Array 10 x 10mm, 300µm Pitch, 2° Divergence, VIS-NIR Coated



Microlens Arrays



Stock **#15-809** 3-4 DAYS

⊖ 1 ⊕

€805,00

ADD TO CART

Qty 1-10	€805,00
Qty 11+	€724,00
Volume Pricing	
Request Quote	
ⓘ Prices shown are exclusive of VAT/local taxes	

Get Product Downloads

Effective Focal Length EFL (mm):
4.80

Substrate: [Fused Silica](#) (Corning 7980)

Coating: VIS-NIR (400-1000nm)
Type: Lens Array
Wavelength Range (nm): 400 - 1000
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±2.0
Lens Profile: Spherical
Pitch (µm): 300.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 2.2
Thickness (mm): 0.90
Thickness Tolerance (mm): ±0.05
Type of Optics: Plano-Convex

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant