

TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS #68-215 • 8.5mm FL • f/1.4

PRIMARY WD: 200MM – ∞



Our TECHSPEC® High Resolution 5 Megapixel Fixed Focal Length Lenses are available in multiple focal lengths and feature multiple versions to optimize for different working distance ranges. Perfect for use on high-end 5 megapixel sensors that require 145 lp/mm resolution, these lenses offer an attractive price-to-performance ratio. All lenses feature locking focus and iris rings and a front filter thread to allow the use of standard optical filters, for increased versatility.

Focal Length:	8.5mm
Minimum Working Distance¹:	75mm
Focus Range¹:	75mm - ∞
Primary Working Distance Range:	200mm - ∞
Length at Near Focus:	44.6mm
Length at Far Focus:	44.3mm
Filter Thread:	M40.5 x 0.5
Maximum Rear Protrusion:	0.74mm
Camera Mount:	C-Mount

Maximum Sensor Format:	2/3"
Aperture (f/#) (lockable):	f/1.4 - f/16
Magnification Range:	0X - 0.037X
Distortion²:	< -6.5%
Object Space NA²:	0.0074
Number of Elements (Groups):	9 (8)
AR Coating:	425 - 675nm BBAR
Weight:	100g

Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"	Sony 2/3"	1"
Field of View^{3,4}	39.7mm - 24.1°	53.3mm - 32.0°	63.7mm - 37.8°	72.0mm - 42.2°	81.6mm - 47.2°	101.5mm - 56.8°	97.0mm - 54.7°	N/A
Field of View^{3,5}	93.1mm - 24.1°	125.0mm - 32.0°	149.3mm - 37.8°	168.5mm - 42.2°	190.8mm - 47.2°	236.7mm - 56.8°	226.4mm - 54.7°	N/A

1. From front of housing 2. At 200mm W.D. 3. Horizontal FOV on standard 4:3 sensor format
4. For focusing range: Min. W.D. - infinite conjugate angular FOV 5. For primary range

Specifications subject to change




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS #68-215 • 8.5mm FL • f/1.4

PRIMARY WD: 200MM – ∞

MTF & DOF: f/2.8
WD: 200mm




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS #68-215 • 8.5mm FL • f/1.4

PRIMARY WD: 200MM – ∞

MTF & DOF: f/4.0
WD: 200mm

TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

Edmund
optics | worldwide

www.edmundoptics.com

TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS #68-215 • 8.5mm FL • f/1.4

PRIMARY WD: 200MM – ∞

MTF & DOF: f/2.8
WD: 500mm




Figure 7: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 8: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

Edmund
optics | worldwide

www.edmundoptics.com

TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS #68-215 • 8.5mm FL • f/1.4

PRIMARY WD: 200MM – ∞

MTF & DOF: f/4.0
WD: 500mm

TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS




Figure 9: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 10: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

Edmund
optics | worldwide

www.edmundoptics.com