

TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS #85-866 • 16mm FL • f/1.8 PRIMARY WD: 300 – 2000mm

Our TECHSPEC® High Resolution 5 Megapixel Fixed Focal Length Lenses are available in multiple focal lengths and feature multiple versions to optimize for different working distance ranges. Perfect for use on high-end 5 megapixel sensors that require 145 lp/mm resolution, these lenses offer an attractive price-to-performance ratio. All lenses feature locking focus and iris rings and a front filter thread to allow the use of standard optical filters, for increased versatility.



TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS

Focal Length:	16mm
Minimum Working Distance¹:	100mm
Focus Range¹:	100mm - ∞
Primary Working Distance Range:	300 - 2000mm
Length at Near Focus:	43.38mm
Length at Far Focus:	41.02mm
Filter Thread:	M25.5 x 0.5
Maximum Rear Protrusion:	0.45mm
Camera Mount:	C-Mount

Maximum Sensor Format:	2/3"
Aperture (f/#) (lockable):	f1.8 - f16
Magnification Range:	0X - 0.077X
Distortion²:	<3%
Object Space NA²:	0.008
Number of Elements (Groups):	9 (7)
AR Coating:	425 - 675nm BBAR
Weight:	120g

Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"	Sony 2/3"	1"
Field of View^{3,4}	24.3mm - 12.83°	32.5mm - 17.09°	38.6mm - 20.28°	43.5mm - 22.76°	49.0mm - 25.58°	60.3 - 29.96	57.8mm - 31.21°	N/A
Field of View^{3,5}	69.4 - 452.9mm	92.8 - 605.3mm	110.4 - 720.4mm	124.2 - 810.5mm	140.1 - 914.1mm	172.3 - 1124.4mm	165.4 - 1077.5mm	N/A

1. From front of housing 2. At 500mm W.D. 3. Horizontal FOV on standard 4:3 sensor format
4. For focusing range: Min. W.D. - infinite conjugate angular FOV 5. For primary range

Specifications subject to change




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**TECHSPEC® HIGH RESOLUTION
FIXED FOCAL LENGTH LENS**
#85-866 • 16mm FL • f/1.8
PRIMARY WD: 300 – 2000mm

**MTF & DOF: f/2.8
WD: 500mm**




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**TECHSPEC® HIGH RESOLUTION
FIXED FOCAL LENGTH LENS**
#85-866 • 16mm FL • f/1.8
PRIMARY WD: 300 – 2000mm

**MTF & DOF: f/2.8
WD: 2000mm**




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**TECHSPEC® HIGH RESOLUTION
FIXED FOCAL LENGTH LENS**
#85-866 • 16mm FL • f/1.8
PRIMARY WD: 300 – 2000mm

**MTF & DOF: f/4.0
WD: 500mm**




Figure 7: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 8: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**TECHSPEC® HIGH RESOLUTION
FIXED FOCAL LENGTH LENS**
#85-866 • 16mm FL • f/1.8
PRIMARY WD: 300 – 2000mm

**MTF & DOF: f/4.0
WD: 2000mm**




Figure 9: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 10: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.