




NOTES:

1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 arcsec
3. COATING (APPLY ACROSS COATING APERTURE)  
 PERFORMANCE SPECIFICATIONS:  
 T(avg): >80 (AVG)% FROM 350-2200nm  
 CUT-ON WAVELENGTH: 390nm
4.  FINE GRIND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS  
 APPLY ACROSS CLEAR APERTURE
6. ROHS EXEMPT




**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**



CUT-OFF FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY



|                 |                      |                      |  |       |                         |              |
|-----------------|----------------------|----------------------|--|-------|-------------------------|--------------|
| REV A           | S1                   | S2                   |  |       |                         |              |
| SHAPE           | PLANO                | PLANO                | THIRD ANGLE PROJECTION  | TITLE | Ø52mm UV CUT-OFF FILTER |              |
| SURFACE QUALITY | 80-50                | 80-50                | ALL DIMS IN  | mm    | DWG NO                  | 54055        |
| BEVEL           | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |  |       |                         | SHEET 1 OF 1 |