



NOTES:

1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)  
 S1: Protected Aluminum (400-700nm)  
 R(AVG) >85% @ 400 - 700nm @ 45°  
  
 S2: NONE
3.  SEAMED EDGES
4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	N/A
SURFACE FLATNESS	4 - 6λ	N/A
CLEAR APERTURE	∅ 19.8 x 26.1	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

22 x 29mm, 4-6λ Mirror

DWG NO

31419

SHEET  
1 OF 1