




NOTES:

1. SUBSTRATE: UV GRADE FUSED SILICA
2. BLOCKING WAVELENGTH RANGE: 250-1100 nm
3. TRANSMISSION: 93%
4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
5. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics**®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	OD6, Ø50mm, 512nm x 25nm, BP FLUORESCENCE FILTER	
SHAPE	PLANO	PLANO			ALL DIMS IN	mm	DWG NO
SURFACE QUALITY	60-40	60-40					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					