
NOTES:


- SUBSTRATE: UV GRADE FUSED SILICA 1.
- 2. COATING (APPLY ACROSS COATING APERTURE) S1 & S2: RABS ≤1.0% @ 250 - 425nm RAVG ≤0.75% @ 250 - 425nm RAVG ≤0.5% @ 370 - 420nm
- 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN <5 ARCSEC

/4.\

FINE GRIND SURFACE

5. **ROHS COMPLIANT**





PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	20-10	20-10	
CLEAR APERTURE	Ø40.00	Ø40.00	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	
•			

		5	Edmund Option	S®
THIRD ANGLE PROJECTION	ϕ	TITLE	50mm DIA., 3mm THICK, UV-AR COATE FUSED SILICA WINDOW	Ο λ/10
ALL DIMS IN	mm	DWG NO	3/0/0	SHEET

36948

DWG NO

ALL DIMS IN