
## NOTES:

- 1. SUBSTRATE: UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS COATING APERTURE) S1 & S2: RABS ≤1.0% @ 250 - 425nm RAVG ≤0.75% @ 250 - 425nm RAVG ≤0.5% @ 370 - 420nm
- 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN <5 ARCSEC
- 4. FINE GRIND SURFACE
- 5. Rohs Compliant



	S1	\$2					
SHAPE	PLANO	PLANO		TITLE	50mm DIA., 6mm THICK, UV-AR COATED λ/10 FUSED SILICA WINDOW		
SURFACE QUALITY	20-10	20-10	THIRD ANGLE				
CLEAR APERTURE	Ø40.00	Ø40.00		1			CULET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	36953	SHEET 1 OF 1