




NOTES:

- 1. SUBSTRATE:
FUSED SILICA
- 2. TEMPERATURE RANGE:
-40 TO +170 °C

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SPECTRAL RANGE	200 - 1500nm
CLEAR APERTURE	22.5mm
ANGULAR TOLERANCE	$0.5 \pm 1^\circ$
TRANSMISSION EFFICIENCY	90%



ALL DIMS IN mm

EO® **Edmund Optics**®

TITLE

0.5° DIFFUSING ANGLE 25mm DIA., UV
HOLOGRAPHIC DIFFUSER

DWG NO

47680

SHEET
1 OF 1