





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

SUBSTRATE	Fused Silica
GROOVE DENSITY (grooves/mm)	830
WAVELENGTH RANGE (nm)	250 - 450
BLAZE ANGLE	19.4°
RoHS	COMPLIANT

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	830 Grooves/mm, 12.7mm Sq, UV Transmission Grating Beamsplitter	
ALL DIMS IN	mm	DWG NO	85289	SHEET 1 OF 1