

NOTES:

1. SUBSTRATE:  
II-VI Infrared ZnSe
2. CENTERING TOLERANCE:  
EDGE THICKNESS VARIATION MEASURED AT THE CLEAR APERTURE OF S1 NOT TO EXCEED 50.8µm
3. COATING (APPLY ACROSS COATING APERTURE):  
S1 & S2: NONE

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**


SPECIFICATIONS SUBJECT TO CHANGE  
WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

4. FINE GRIND SURFACE

5. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$

6. SURFACE ROUGHNESS: 50 Å



COEFFICIENT TABLE 5.	
COEFFICIENT	S1
SEMI-DIAMETER	6.350000E+00
(1/RADIUS)	5.612302E-02
k	-1.023521E+00
D	0.000000E+00
E	-1.320812E-05
F	-1.686006E-08
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

	S1	S2
SHAPE	CONVEX	PLANO
RADIUS	17.818	INFINITY
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø11.43	Ø11.43
POWER at 632.8nm	2.0 RINGS	2.0 RINGS
IRREGULARITY at 632.8nm	1.0 RING	1.0 RING
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL (AT 10.6µm)	(12.70)
BFL (AT 10.6µm)	(11.25)



ALL DIMS IN mm



**Edmund Optics®**

TITLE	DWG NO	SHEET
12.7mm Dia. x 12.7mm FL Uncoated, Zinc Selenide Aspheric Lens	39470	1 OF 1