



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



FOCAL LENGTH FL (mm)	10.0
MAGNIFICATION	20X
MOUNTING THREAD	M26 x 36 TPI
NUMERICAL APERTURE NA	0.28
WORKING DISTANCE (mm)	30.5
LENGTH EXCLUDING THREADS (mm)	64.5
MAXIMUM DIAMETER (mm)	34
TYPE	Microscope Objective
COMPATIBLE TUBE LENS	Focal Length: 200mm
DEPTH OF FOCUS (μm)	3.5
ENTRANCE PUPIL (mm)	5.8
FIELD OF VIEW, 1/2" SENSOR	0.32 x 0.24mm
FIELD OF VIEW, 18 DIAMETER FIELD EYEPIECE (mm)	0.9
FIELD OF VIEW, 2/3" SENSOR	0.44 x 0.33mm
FIELD OF VIEW, 24 DIAMETER FIELD EYEPIECE (mm)	1.2
RESOLVING POWER (μm)	1.0
WAVELENGTH RANGE (nm)	435 - 655
RoHS	Exempt

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics**®

THIRD ANGLE PROJECTION

TITLE

20X Mitutoyo Plan Apo SL Infinity Corrected Objective

ALL DIMS IN

mm

DWG NO

46398

SHEET
1 OF 1