




NOTES:

1. MODEL NUMBER: Model B
2. APERTURE (f/#): f/3.9
FOCAL LENGTH FL (mm): 74.00
LINEAR DISPERSION (nm/mm): 7.27
3. RESOLUTION (nm)
100um SLIT WIDTH: 0.73
150um SLIT WIDTH: 1.09
300um SLIT WIDTH: 2.18
600um SLIT WIDTH: 4.36
4. SLIT WIDTH (um): 300.00
SLIT HEIGHT (mm): 4.00
5. STRAY LIGHT (%): ≤0.003
6. WAVELENGTH RANGE(nm): 200 - 800
WAVELENGTH ACCURACY (%): ±0.2 of λ
WAVELENGTH READABILITY (nm): 0.2
WAVELENGTH REPRODUCIBILITY (%): ±0.15
7. TYPE OF OPTICS: 2cm² Square, Holographic Grating
BLAZE WAVELENGTH (nm): 250.00
GROOVE DENSITY (grooves/mm): 1800
8. DAMAGE THRESHOLD,
CW: 40 Watt/cm²
PULSED: 350 mJ/cm² @ 200ns
9. MOUNTING HOLE DIMENSIONS: 1/4-20 THREADED MOUNTING HOLES



**FOR INFORMATION ONLY;
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO
CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR
REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	200 - 800nm, Manual Mini-Chrom Monochromator	
ALL DIMS IN	mm	DWG NO	37597	SHEET 1 OF 1