


NOTES:

- 1. ALLOWABLE OPTICAL MATERIAL:
OPTICAL GRADE GERMANIUM
- 2. CENTERING TOLERANCE (AT 587.6nm):
BEAM DEVIATION: <3 ARCMINUTES
- 3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE

4. EDGES DIAMOND TURNED



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING**

	S1	S2			 Edmund Optics®	
SHAPE	CONVEX	CONCAVE	EFL (AT 10.6μm)	(25.00)		
RADIUS	28.32	42.46	BFL (AT 10.6μm)	(23.34)	TITLE	ø25mm x 25mm FL, UNCOATED GERMANIUM MENISCUS LENS
SURFACE QUALITY	60 - 40	60 - 40	ALL DIMS IN	mm	DWG NO	87955
CLEAR APERTURE	≥ ø22.50	≥ ø22.50				
BEVEL MAX FACE	0.3mm x 45°	0.3mm x 45°				