



FOCAL LENGTH (EFL): $22,5 \pm 0,23$

BACK FOCAL LENGTH (BFL): 20,5

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	15,12±0,015 CX	GLASS N-SF5 673/322	R	∞ PL
∅e	14		∅e	14
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
SCALE: NONE
λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 15,0mm Dia, x 22,5mm FL Uncoated, Plano-Convex Lens

DWG NO 32004

SHEET SIZE A4
SHEET 1 OF 1