



FOCAL LENGTH (EFL): 200 ± 2
 BACK FOCAL LENGTH (BFL): $196,92$

1 AR COATING:
 $\frac{1}{4}$ WAVE MgF₂ @ 550nm
 R(AVG) < 1,75% FROM 400-700nm (N-BK7)

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$104,6 \pm 0,105$ CX	GLASS N-K5 523/595	R	∞ PL
Øe	39		Øe	39
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,91'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	$\lambda = 587,6$ nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	40,0mm Dia, x 200,0mm FL, MgF ₂ Coated, PCX N-K5 Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	DWG NO	32899	SHEET SIZE
INDICATIONS IN ACCORDANCE WITH ISO 10110			mm			SHEET	1 OF 1