



FOCAL LENGTH (EFL):  $125 \pm 1.25$   
 BACK FOCAL LENGTH (BFL):  $122.65$

1 AR COATING: 1064nm V-COAT  
 $R(\text{ABS}) < 0.25\% @ 1064\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$57,308 \pm 0,057 \text{ CX}$	GLASS FUSED SILICA 458/678	R	$\infty \text{ PL}$
$\phi_e$	24		$\phi_e$	24
3/	3 (0,5) $\lambda=632,8 \text{ nm}$		3/	3 (0,5) $\lambda=632,8 \text{ nm}$
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 25mm Dia, x 125mm FL 1064nm V-Coat, UV PCX Lens

DWG NO 34144

SHEET SIZE A4  
 SHEET 1 OF 1