



FOCAL LENGTH (EFL):  $6 \pm 0,06$   
 BACK FOCAL LENGTH (BFL):  $5,37$

1 AR COATING:  
 $\frac{1}{4}$  WAVE MgF2 @ 550nm  
 R(AVG) < 1,75% FROM 400-700nm (N-BK7)

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	5,88±0,006 CX	GLASS N-BK7 517/642	R	5,88±0,006 CX
Øe	2,5		Øe	2,5
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	5,8'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION				
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	3mm Dia, x 6mm FL, MgF2 Coated, Double-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm	DWG NO	45130	
INDICATIONS IN ACCORDANCE WITH ISO 10110						SHEET 1 OF 1