



FOCAL LENGTH (EFL): 100 ±1

BACK FOCAL LENGTH (BFL): 98,35

- 1 AR COATING: VIS-NIR  
 $R(\text{ABS}) \leq 0,25\%$  AT 880nm @ 0° AOI  
 $R(\text{AVG}) \leq 1,25\%$  FROM 400-870nm @ 0° AOI  
 $R(\text{AVG}) \leq 1,25\%$  FROM 890-1000nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	51,68±0,052 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE    λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 12,0mm Dia, x 100,0mm FL, VIS-NIR, Inked, Plano-Convex Lens

DWG NO 45490INK

SHEET SIZE A4    SHEET 1 OF 1